Cel Email Email WEB 719-580-3642, 303-999-6837 Sales@AppliedMetrologyUSA.com Support@AppliedMetrologyUSA.com www.AppliedMetrologyUSA.com

AFM Cube Smoke Studies Fogger



Fogger Design	AFM Cube Smoke Studies Fogger is for airflow visualization studies and smoke studies. This cleanroom fogger uses De-ionized (DI) water, Sterile water or WFI (Water for Injection) water to produce a dense, pure fog with 8-10 micron fog droplets using 20 ultrasonic piezos; providing good fog volume in a compact stainless-steel enclosure, made from 316L stainless. One 80 mm Fog Outlet connects to a variety of optional accessories and has two Carry Handles and a water cavity holding 9-9.5 Liters of De-Ionized water, WFI water, or Sterile water.
Fog Application	Pure fog in BSCs, small Barrier Isolators, Glove Boxes, bio-Safety Cabinets, Airflow Hoods. One 80mm Fog Outlet, adjustable fog velocity and adjustable fog volume with 12 optional fogger accessories to visualize airflow turbulence.
Fog Volume	about 0.71 Cubic Meters pure fog per minute through one 80mm fog outlet
Fog Duration	about 45 minutes at max fog volume; or 70 minutes at lowest fog volume
Visual Airflow Distance	about 7-8 feet using the single 80mm fog outlet
Liquids Used	De-Ionized (DI) Water, Sterile Water or Water for Injection (WFI) Water
Optional Accessories	1.2 M x 80mm Fog Rake, Wireless Remote Control, 5Mx80mm Fog Hose, Rolling Carry Case, 80mm Y adaptor with Butterfly Valves, LED Multi-Color Fog Contrast Light
Power	Internal power supply: 115 VAC, 60 Hz or 220 VAC, 50 Hz; or 100VAC

AFM Cube Smoke Studies Cleanroom Fogger is used in smoke studies and airflow visualization studies, producing about 0.71 cubic meters of pure visual fog for about 45 minutes duration. The fog output can be controlled in volume and velocity using the touch pad controls on the control panel. Fog produced is generated through 20 ultrasonic piezos, creating a pure fog that is 8-10 microns in diameter, and evaporates back to the same air we breathe. The AFM Cube is produced with a 316L electro-polished stainless-steel enclosure, providing two carry handles and a single 80mm fog outlet. The AFM Cube Smoke Studies fogger is an easy smoke generator to use in smoke studies of 2x6 Airflow Hoods, Gloveboxes, BSCs, etc.